

AmfiBi Double HighBack

EL

AmfiBi Double HighBack is a further development of our much appreciated AmfiBi concept. It is equipped with a high, upholstered back with upholstered back including neck rest and integrated seat with rear opening. The high backrest provides soft yet stable support and its lower section is fitted with a pliant lumbar support for additional comfort. The seat with the opening to the rear was designed to meet the wishes of GATE customers; it provides a natural, more hygienic working method.



High, upholstered backrest

The high backrest provides soft yet stable support. It is easy to clean and can be replaced as necessary.

Integrated neck rest

The integrated height-adjustable neck rest is available in two sizes, M and L.

Tilt function

AmfiBi Double can be inclined 5 degrees forward to 25 degrees rearward, which makes it easy to use for personal hygiene and when sitting or getting up. The tilt function also improves the working environment and reduces strain on personnel.

Pliant lumbar support

The lower section of the backrest is fitted with a pliant lumbar support for additional comfort.

Lockable armrests

The armrests can be flipped up and locked in position to make it easier for the patient to be of help with the transfer.

Integrated seat with the opening to the rear

The seat has a soft, resilient, ergonomic design for the best comfort possible. The opening to the rear provides the carer with a natural, more hygienic working method.

Swing-away, detachable footrests

Flip-up, swing-away, detachable footrests with heel restraints to prevent the patient's feet from sliding off in the tilt position are fitted as standard.

Lockable castors

All four castors are lockable.

Plastic or metal

A guide is available for AmfiBi as an accessory. Note that the guide is available in different versions to suit plastic or metal bedpans.

Electronics for height and tilt operation

The high-backrest design means that the electronics for height and tilt operation have been located in a protective box at the rear and that wiring has been integrated in a better way than previously.

For accessories see page 7.

Technical specifications

CE marked according to MDD 93/42/EEC

Part No.	Product	Max user weight	Width	Internal dimensions/armrests	Seat height	Seat depth	Tilt
56-275	AmfiBi Double HighBack	150 kg	60 cm	50 cm	53-82 cm	45 cm	5 degrees forward to 25 degrees rearward